


DT - SOUTHWEST

P.O.# 05771

NOZZLES WP1002 / SEAMS WP3002 OR WP3004

NOZZLE SCHEDULE								VESSEL DESIGN SPECIFICATIONS				REVISIONS			TITLE	
H								DESIGN & CONSTRUCTION IN ACCORDANCE WITH SECTION VIII DIV. 1 ASME CODE FOR PRESSURE VESSELS 1983 EDITION & ADDENDA TO SUMMER '85	NO	DATE	BY	30" DIA. x 8'-0" (VERT.) 150# ASME INTER-COOLER				
G	1	3/4"	CPLG.	3000#	SA 105	OIL DRAIN		SHELL SA 516-70 .250 NOM.	1	2/15/86	DRB	 2010 FOUNTAIN ROAD, BRYAN, TEXAS 77801				
F	1	1 1/4"	CPLG.	3000#	SA 105	LIQ. MAKE-UP		HEADS SA 516-70 2:1 ELLIPT .313 MIN.	2							
E	1	3/4"	CPLG.	3000#	SA 105	RELIEF		RT NO HT NO CA 0	3							
D	1	1 1/4"	CPLG.	3000#	SA 105	LIQUID OUT		M.A.W.P. 150 PSI 300 TO -20° F	4							
C	2	1 1/4"	CPLG.	3000#	SA 105	FLT. COL. CONN.		HYDROTEST 225 PSI	5							
B	1	5"	PIPE	S/40	SA 53B OR 106B	BOOST. DISCH. IN	13 1/2"	PAINT: SHOP PRIMER	DRAWN BY WRS			SCALE 1" = 1'-0"	DRAWING NO. C00037			
A	1	5"	PIPE	S/40	SA 53B OR 106B	SUCTION OUT	7"	TOLERANCE:	CHECKED BY DRB			DATE 2-05-86	REV. 1			
ITEM	QTY	SIZE	TYPE	RATING	MATERIAL	SERVICE	LGTH	REINFORCEMENT								