

Cherry Burrell High Pressure Pump / Homogenizer

Mfg: Cherry-Burrell

Model: SS 2100 VBR

Stock No: SPGT014.65

Serial No: 164587 87

Cherry Burrell High Pressure Pump / Homogenizer. Model: SS 2100 VBR. S/N: 164587 87. Single stage bypass valve. Plunger Size: 1-½ in. diameter. Nominal capacity: 21 gpm. Poppet seat valve cylinders. Maximum operating pressure: 1,500 PSI. Baldor electric motor, 40 hp, 1760 rpm, 575 V, 39 amps, 60 Hz, 3 phase. Driver pulley: 4 in. dia. Driven pulley: 24 in. dia. Ratio: 6.0:1. Final rpm: 293. Inlets: (2) 2 in. diameter I-Line fitting. Outlet: (1) 7/8 in. discharge threaded fitting. Unit weight: 2512 lbs. Overall dimensions: 4 ft. 2 in. L x 2 ft. 8 in. W x 3 ft. 8-3/4 in. H.(ACN645).













