

Hansen Technologies Hermetic Centrifugal Pump

Mfg: Hansen Technologies

Model: CAM2/3

Stock No: RPCN511

Serial No:

Hansen Technologies Hermetic Centrifugal Pump. Order No: 411001011/031-01. Flow rate for a new pump is approximately 50 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Impeller diameter: 4.48 in. Nominal pressure: 362 psi. AGX Motor, 6.3 hp (4.7 kW), 3380 rpm, 440 V, 7.5 amps, 60 Hz, 3 phase. Inlets: (1) 1-1/2 in. dia. flanged port. Outlets: (1) 1 in. dia. flanged port. Overall dimensions: 2 ft. L x 9 in. W x 10 in. H.(ACN75).



