

APV Crepaco Sanitary Centrifugal Pump


Mfg: APV Crepaco

Model: 6V2

Stock No. pBBCF087B.

Serial No. F-7229-89

APV Crepaco Sanitary Centrifugal Pump. Model: 6V2. S/N: F-7229-89. Impeller diameter: 6 in. Seal option: Single mechanical. Reliance Electric Motor. 2 hp, 1725 rpm, 208-230/460 V, 6.4/3.2/2.6 amps, 60 Hz, 3 phase. Inlets: (1) 2-1/2 in. dia. S-line fitting. Outlets: (1) 1-1/2 in. dia. S-line fitting. Overall dimensions: 1 ft. 7 in. L x 1 ft. W x 9-1/2 in. H.





1414055M-XP	FR 145TC	TYPE	
7	1725	208-230	* 60
		460/575	
CONT	F	INS TYPE	AMB 40 NEMA DESIGN
CERTIFIED STD 29			
4-6.4/5.3/7.6			
10 190/580V 50HZ			
RELIANCE ELECTRIC COMPANY			
CLEVELAND, OHIO 44117			

1414055M-XP	FR 145TC	TYPE	P 1PH 3
7	1725	208-230	* 60 1.0
		460/575	
CONT	F	INS TYPE	AMB 40 NEMA DESIGN
CERTIFIED STD 29			
4-6.4/5.3/7.6			
10 190/580V 50HZ			
RELIANCE ELECTRIC COMPANY			
CLEVELAND, OHIO 44117			

1414055M-XP	FR 145TC	TY	
7	1725	208-230	* 60
		460/575	
CONT	F	INS TYPE	AMB 40 NEMA DESIGN
CERTIFIED STD 29			
4-6.4/5.3/7.6			
10 190/580V 50HZ			
RELIANCE ELECTRIC COMPANY			
CLEVELAND, OHIO 44117			