

## Screw Conveyor Stainless Steel

Mfg:

Model:

Stock No. 55.205

Serial No.

### Screw Conveyor Stainless Steel

- U.S. Electrical motor 3.4 hp, 3 phase, 230/460 V, 2.8/1.4 amps,
- Gear Ratio 11.25, final rpm 155. Motor rpm 1,750.
- Output torque 276.
- Inside dimensions 120 in. L x 12-1/2 in. W x 12 in. H.
- Screw 11 ft. diameter.
- 4 legs with casters (2) 28 in. high and (2) 60 in. high.

