

Single Wall Tank, Stainless Steel, 3,000 gallon. Motor with gearbox control. Drive information Model 21 - 4EB24-16A7. M.O 6010-0804, Date 4/60, Input 1750 rpm, Output 11 rpm, ratio 159.6, Rating 184 hp. Falk Enclosed Gear Drive, ID no. P14x3237N-XR, 2 hp, 230/460 volt, 5.4/2.7 amps, 1725 rpm, 40 def C. amb, continuous duty, 60 hz. (4) Legs 39 in. H. Inside dimensions 7 ft. diameter x 13 ft. H, Overall dimensions 100 in. diameter x 18 ft. H.

