

Cherry-Burrell Stellar-Flo 2500 Series Homogenizer – 5500 PSI

Mfg: Cherry-Burrell

Model: HD-6

Stock No: tANIP01

Serial No: 259797

Cherry Burrell Stellar-Flo 2500 Series Homogenizer. Model: HD-6. Capacity 1000 gph Maximum Operating Press. 5500 psi. Pressure and flowrate can be modified/adjusted to suit your needs. Currently setup as a pump, but homogenizing valve(s) can be added. Tapered seat ball valves. Plunger size diameters 1-7/8 in. One stage valve. 316 stainless steel contact surfaces. Inlets /outlets (1) 2 in. s-line. (1) 1 in. acme. (1) 5/8 in. shut on/off American valve. (1) Anderson gauge. US motor: 60 Hp, 1500/1800 rpm, 220 volts, 147/147 amps, 50/60 Hz, 3 phase. Overall dimensions: 6 ft. 11-1/2 in. L. x 4 ft. 1 in. W. x 4 ft. 4 in. H.







