

## Recold Ammonia Recirculating Evaporator




Mfg: Recold

Model:

Stock No. tMHCS010.

Serial No.:

Recold Ammonia Recirculating Evaporator. Fins per inch: 5. (3) 18 in. dia. fans. (3) Dayton Motors, 1/2 hp, 1725/1425 rpm, 208-220/440 V, 2/1 amps, 60/50 Hz, single phase. Inlets: (1) 1-1/4 in. dia. port, (1) 2 in. dia. port. Outlet: (1) 2 in. dia. port. Overall dimensions: 6 ft. 5-1/2 in. L x 2 ft. 11-1/2 in. W x 3 ft. 3 in. H.





**Dayton** SPLIT PHASE A.C. MOTOR

A HP. 1/3 R.P.M. 1725  
 0 A. 2.8 HZ. 60  
 CONT. INSUL. CLASS A PH. II  
 BRGS. SLEEVE CODE M  
 A 3.2 AMB. 40 °C  
 SA55JXEC0-2814

PROTECTED AUTO

TEETH  
 NUT REQ'D WITH  
 CONDUIT FITTING

REOIL EACH BEARING SAE 20 OIL  
 CONTINUOUS DUTY-EVERY YEAR  
 INTERMITTENT DUTY-EVERY 2 YEARS  
 OCCASIONAL DUTY-EVERY 5 YEARS

ELECTRIC MFG. CO. CHICAGO 60648, U.S.A.

CONNECTIONS

RED 2 LINE  
 BLK. 4 LINE

TO REVERSE ROTATION  
 INTERCHANGE RED & BLK LEADS

**Dayton** SPLIT PHASE A.C. MOTOR

MODEL 8K717A HP. 1/3 R.P.M. 1725  
 V. 208/230 A. 2.8 HZ. 60  
 TIME RATING CONT INSUL. CLASS A PH. II  
 FRAME 48 BRGS. SLEEVE CODE M  
 S F T35 S F A 3.2 AMB. 40 °C  
 MTR. REF. NO. SA55JXEC0-2814

THERMALLY PROTECTED AUTO

E 47479  
 L22450  
 MFG. NO. E79 7

TEETH  
 NUT REQ'D WITH  
 CONDUIT FITTING

REOIL EACH BEARING SAE 20 OIL  
 CONTINUOUS DUTY-EVERY YEAR  
 INTERMITTENT DUTY-EVERY 2 YEARS  
 OCCASIONAL DUTY-EVERY 5 YEARS

DAYTON ELECTRIC MFG. CO. CHICAGO 60648, U.S.A.

WARNING: MOTOR MUST BE PROPERLY GROUNDED AND TERMINAL COVER  
 MUST BE IN PLACE TO PREVENT POTENTIAL ELECTRICAL SHOCK

CONNECTIONS

RED 2 LINE  
 BLK. 4 LINE

TO REVERSE ROTATION  
 INTERCHANGE RED & BLK LEADS