

Cherry-Burrell Extra Heavy Duty Oval Votator 6 x 72

Mfg: Cherry-Burrell

Model: 10672L

Stock No: tPPMI001

Serial No: 81153VA

Cherry-Burrell Extra Heavy Duty Oval Votator 6 x 72. Model: 10672L. S/N: 81153VA. Nat'l Bd: 702. 316 Stainless steel construction, with control panel. Shell MAWP @ 375 °F: 400 psi. Jacket MAWP @ 375 °F: 100 psi. Shaft diameter: 5 in. Scraper dimensions: 6 in. L x 2 in. W. Reliance Electric Motor, 20 hp, 1160 rpm, 230/460 V, 60/30 amps, 60 Hz, 3 phase. Reeves variable speed drive, 14 ratio, output speeds max/min 190/28.6 rpm. Inlets: (1) 1-1/2 in. NPT (female-jacket) , (1) 1-1/2 in. dia. S-line (product), (2) 1/2 in. dia. male ferrules. Outlets: (1) 1-1/2 in. dia. NPT (female-jacket), (2) 1-1/2 in. dia. S-line (product discharge through a divert valve), (2) 1/2 in. dia. male ferrules. Overall dimensions: 13 ft. 4-1/2 in. L x 3 ft. W x 6 ft. 4 in. H. (ACN 543).













