

## Howe Corporation Ice Flaker – 3 Tons

**Mfg: Howe Corporation**

**Model: 31-E**

**Stock No: AAMG197.a**

**Serial No: 36962**

1984 Howe Corporation Ice Flaker. Model: 31-E. S/N: 36962. Refrigerant: R-12 or 502. Rated capacity: 3 tons per day at respective water and air temperatures of 70°F and 90°F. Specifications include: .52 KWH/100lbs. ice. Design pressure: 150 psi. Design temperature: -5 degree F. Lincoln drive motor, ½ hp, 1725 rpm, 115/208-230 V, 8.0/4.1 amps, 60 Hz, single phase. Grove gear reducer: Ratio: 600. Final rpm: 3. Required refrigeration: 51,150 BTU/Hr. Inlets: (1) 6 in. L x 4 in. W, (1) 1 in. dia. port. Outlets: (1) 1 in. dia. port, (1) 1/2 in. dia. port. Overall dimensions: 3 ft. 11 in. L x 3 ft. 4 in. W x 3 ft. 7 in. H. Approximate shipping weight: 900 lbs.(ACN141-84).







