

Stainless Steel Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No. 35.343a

Serial No.:

Stainless Steel Shell and Tube Heat Exchanger. Tube material: 316 stainless steel. Number of passes: 1. Number of tubes: 110. Tube dimensions: 2 in. dia. x 9 ft. 11 in. L. Heat transfer surface area: approx. 570.86 sq. ft. Tube volume: 175 gal. Inlets: (1) 8 in. dia. port, (1) 1 in. dia. port, (1) 3 in. dia. S-Line. Outlets: (1) 3-1/2 in. dia. port, (1) 1 in. dia. port, 16 in. L x 16 in. W manway. Overall dimensions: 4 ft. 11-1/2 in. L x 3 ft. 11 in. W x 13 ft. 9 in. H.

