

## Evapco Evaporative Condenser – 650 Tons

**Mfg: Evapco**

**Model: PMC-650N**

**Stock No: AANF321.80**

**Serial No: 868021**

Evapco Evaporative Condenser. Model: PMC-650N. Serial No: 868021. Nominal capacity: 650 tons using R-22 at 105°F condensing temperature, 40°F suction temperature, and 78°F wet bulb temperature. R-717 (ammonia) capacity rating: 462 tons at 96.3°F condensing temperature, 20°F suction temperature and 78°F wet bulb temperature. Includes (2) 10 kW pan heaters 230/60/3 with thermostat and low water cutoff. Approximate shipping weight of evap condenser: 34,380 lbs. Evap condenser overall dimensions: 27 ft. L x 9 ft. 11-3/4 in. W x 13 ft. 9-1/2 in. H.





