

Frick RWB II 100 H Screw Compressor Package – 250 HP

Mfg: Frick

Model: RWB II 100 H

Stock No: BDPC492.75

Serial No: S0002BFMPLHCA3

Frick RWB II 100 H Screw Compressor Package. Model: RWB II 100 H. Serial No: S0002BFMPLHCA3. S/O: 260729 01. R717. Max PSI: 300. Package year: 1982. The original compressor was removed then replaced with the current 1995 Frick Rotary Screw Compressor model/serial no. TDSH193S2156C, volume ratio: 2.2-5.0, maximum driver speed rpm 4500, design pressure: 350 PSIG. Frick Oil Separator Vessel, nat'l bd. 51930, MAWP: 300 PSIG at -20/200F, year: 1982. The RWB-II-100 model is capable of producing 213 tons at 236 bhp with a 20°F suction temperature, 95°F condensing temperature, 10°F liquid subcooling. Marathon Electric Motor: 250 HP, 3565 RPM, 460 V, 230 amps, SF 1.15, 60 Hz, 3 phase, 445TC frame. Frick RWB II micro controller. *Note: controller will not power up. Overall dimensions: 11 ft. 11 in. L x 4 ft. 4 in. W. x 6 ft. 7 in. H.





