

## Elliot Manufacturing Pasteurizer/Cooler

Mfg: Elliot Manufacturing

Model: 8X40

Stock No. BFLV288.46

Serial No. 20670

Elliot Pasteurizer/Cooler. Model: 8X40. S/N: 20670. Stainless steel. Belt width: 96 in. Maximum aperture/clearance above belt: 93 in. W x 10 in. H. Overhead sprayers, fed by multiple distribution manifolds, pasteurize/cool product. System is equipped with (3) 12 in. L x 12 in. W x 24 in. H side-mounted waste tanks. Infeed/exit height: 38 in. Inlets: (1) 3 in. dia. S-line fitting (cold/hot process), (1) 3 in. dia. bevel fitting (CIP), (2) 13 in. L x 10 in. W infeed ducts. Outlets: (1) 3 in. dia. threaded fitting (waste), (1) 20 in. dia. vent, (2) 29 in. dia. vents. Overall dimensions: 53 ft. 4 in. L x 10 ft. W x 84 in. H. (2) Scot 55 Centrifugal Motorpumps. Model: 9089K148, size: 3x3. (2) U.S. Motors, 10 hp, 3505 rpm, 208-230/460 V, 27.1-24.2/12.1 amps, 60 Hz, 3 phase. Air Blast Inc. Air blowoff system, 4 in. dia. air vent for air knife. Stainless steel control panel.





