

Baltimore Aircoil Company Evaporative Condenser - 200 tons

Mfg: Baltimore Aircoil Company

Model: CPA-200A

Stock No.: BNCA217

Serial No.: 66-1604

Baltimore Aircoil Company Evaporative Condenser. Model: CPA-200A. S/N: 66-1604. Nominal rated capacity: 200 tons using R-22 at 105°F condensing, 40°F suction and 78°F web bulb temperatures. 144 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Fans: (4) 3 ft. dia. Displacement: 57,000 cfm. Manways: (4) 1ft. 5 in. dia. openings. (2) Lincoln electric motors, 5 hp, 1725 rpm, 230/460 V, 13.8/6.9 amps, 60 Hz, 3 phase. Inlets: (1) 4 in. dia. flanged port, (2) 3 in. dia. ports. Outlets: (2) 1 in. dia. ports, (2) 2 in. dia. ports. Approximate shipping weight: 18,000 lbs. Overall dimensions: 13 ft. 10 in. L x 9 ft. W x 9 ft. 4 in. H.(ACN280).







