

2002 Trane Odyssey Condensing Unit- 10 Ton


Mfg: Trane

Model: TTA120A400EA

Stock No. CAM204.

Serial No. 2335UPNAD

2002 Trane Odyssey Condensing Unit- 10 Ton. Model TTA120A400EA. S/N: 2335UPNAD. Outdoor use only. Test pressure Hi/Lo: 375/150 psi. Refrigerant: R-22. Minimum ckt amps: 25.3. Trane Scroll Compressor, Model: CSHB100K0D0C, S/N: 03B18522, 340-460/414-508 V, 118 LRA, 60 Hz, 3 phase. Inlets: (1) 1-1/4 in. dia. copper pipe. Outlets: (1) 3/8 in. dia. copper pipe. Overall dimensions: 42 in. L x 51-1/2 in. W x 40 in. H.





Condensing Unit Specifications

Nominal Tons	EER/IPLV1	Net Capacity (MBH)	Dimensions H x W x L	Ship Weight
7	10.3 / j ^a	89.0	39 x 34 x 41	370
10(2)	10.3 / 11.2	122.0	39 x 34 x 51	481
10(3)	10.3 / j ^a	124.0	39 x 34 x 51	443
10(4)	10.3 / 12.8	122.0	39 x 34 x 51	492
12	9.8 / 11.0	144.0	39 x 34 x 51	481
15(2)	9.7 / 10.9	176.0	39 x 34 x 88	764
15(4)	9.7 / 13.0	176.0	39 x 34 x 88	765
20	9.7 / 10.9	238.0	44 x 44 x 93	945

Notes:

1. EER/IPLV is condensing unit with matched Trane air handler.
2. Dual compressor.
3. Single compressor.
4. Dual manifolded compressors.