

## Spirax Sarco Condensate Recovery System

Mfg: Spirax Sarco

Model:

Stock No. DTTC2108.

Serial No.:

Spirax Sarco Condensate Recovery System. Condensate receiver- 40 gal. Inside straight-wall dimensions: 1 ft. 4 in. dia. x 4 ft. L. Spirax Sarco Pressure Powered Pump, Size: 2x3, B.M: 69422, PMA: 150 psig (10.3 barg), PMO: 125 psig (8.6 barg), TMA: 450°F (343.4°C). Taylor Valve, S/N: 2742-1, P/N: 211SD12000107, size: 1/2, set pressure: 100 psig, capacity: 640 lb/hr, range: 92-114. Inlets: (2) 1 in. dia. ports, (1) 3/4 in. dia. port. Outlets: (1) 1-1/2 in. dia. port, (1) 1 in. dia. port, (1) 3/4 in. dia. FNPT fitting. Overall dimensions: 5 ft. 7 in. L x 3 ft. 7 in. W x 7 ft. 4 in. H.



