



**NOTES:**

1. (M) -FAN MOTOR LOCATION
2. MAKE-UP LOCATED 4 3/4" FROM CONNECTION END.
3. MAKE-UP WATER PRESSURE 20psi MIN. 50psi MAX.
4. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING.
5. HEAVIEST SECTION IS UPPER SECTION.
6. \* APPROXIMATE DIMENSIONS. DO NOT USE FOR PRE-FABRICATION OF CONNECTING PIPING.
7. MPT DENOTES FEMALE PIPE THREAD. FPT DENOTES FEMALE PIPE THREAD. BFW DENOTES BEVELED FOR WELDING.
8. SERIES FLOW PIPING AND AUX. CROSSOVER DRAIN BY OTHERS.

WEIGHTS			NO. SHIPPING SECTIONS
SHIPPING	OPER.	HEAVIEST SECTION	
8470	12970	7250	2

**MODEL NUMBER:** ATW-68B2 CLOSED CIRCUIT COOLER

**CERTIFIED FOR** JOSEPH DAVIS CO. **PROJECT:** AFPS

**CUSTOMER ORDER NO.** E9004-399 **EVAPCO NO.** 992414

**CAPACITY** 250 GPM OF 30% PROPYLENE GLYCOL 95 °F IN 85 °F OUT 75 °F E.W.B.

**FAN MOTOR HP** (1) 10 **ELEC. SPEC.** 460/60/3

**PUMP MOTOR HP** (1) 2 **ELEC. SPEC.** 460/60/3

**REMARKS:** SERIES FLOW COILS. UNIT FURNISHED WITH ELECTRIC WATER LEVEL CONTROL PACKAGE, (1) VIBRATION CUTOFF SWITCH, (4) VICTAULIC COIL CONNECTIONS AND STAINLESS STEEL BASIN. COIL PRESSURE DROP 6.0 PSI. DRIVES SIZED FOR 0" ESP.



**CLOSED CIRCUIT COOLER**

DMV 3/4/99  
**WA080908ERB-08**