

Flake Ice Generators

Industrial Ice Machines



Geneglance
Ice Engineering Excellence

Flake Ice Generators

Industrial Ice Machines



Water	MODEL	PRODUCTION KG /24H	FLUID	DIMENSIONS LxWxH (CM)	WEIGHT (KG)	INSTALLED POWER (W)
-------	-------	--------------------	-------	-----------------------	-------------	---------------------


Land-based models

Water	MODEL	PRODUCTION KG /24H	FLUID	DIMENSIONS LxWxH (CM)	WEIGHT (KG)	INSTALLED POWER (W)
Fresh Water	F15	300 - 500 kg	R22 R404A	52 x 36 x 60	50	160
	F30	600 - 1 000 kg		65 x 50 x 70	90	250
	F90	1 600 - 3 500 kg		89 x 73 x 126	250	250
Sea Water	F90 sw	3 000 kg		90 x 70 x 126	250	305
Fresh Water	F200*	4 500 - 6 500 kg	R22 R717 R404A	120 x 92 x 176	720	320
	F250*	7 000 - 10 000 kg		130 x 97 x 205	900	320
	F600*	10 000 - 14 000 kg		150 x 120 x 205	950	390
	F800*	14 000 - 20 000 kg		155 x 155 x 310	2500	850
	F900*	20 000 - 30 000 kg		195 x 195 x 310	3100	850
	F2000*	40 000 - 50 000 kg		244 x 244 x 310	5000	1150

On-board models


Water	MODEL	PRODUCTION KG /24H	FLUID	DIMENSIONS LxWxH (CM)	WEIGHT (KG)	INSTALLED POWER (W)
Fresh Water	F30 M	1 000 kg	R22 R404A	75 x 50 x 120	90	215
	F100 M	2 500 kg		90 x 70 x 160	220	305
Sea Water	F100 sw	2 700 kg		90 x 70 x 150	220	305

- * Each ice generator is available :
- either with flood bottle (ABF version) for feeding with high pressure liquid.
 - or without flood bottle (SBF version) for feeding with low pressure liquid (flooded system).



• DRY AND SUBCOOLED ICE

- Stationary and insulated cylinder.
- Few moving parts liable to wear and tear.
- Little mechanical constraints.
- Optimum thermal exchange.
- Compatible with all modern refrigerants.
- CE and ASME Compliant.
- Manufacturing under independent survey.
- Food compatibility : *stainless steel water path for models up to 10 tons. Cleaning-in-place optional.*



- 1 Heavy-duty gear reducer
Adjustable speed
- 2 Flood bottle
- 3 Helical reamer
Continuous ice harvesting
- 4 Refrigerant Liquid Level Control
- 5 Double wall stationary drum
Pressure tested at 26 bars - no sealed bearings
- 6 HP liquid line
- 7 CFC-free insulation with PVC
- 8 Solenoid valve
- 9 Rubber wiper
- 10 Dry and sub-cooled flake-ice
Large heat-exchange surface area
- 11 Hand-throttle valve
- 12 Evaporating surface
High-conductivity corrosion shield
- 13 Salt dosing pump
- 14 Heavy-duty water pump



Refrigeration Division of the GEA Group

GEA Geneglace s.a.s.

ZAC de la Forêt – 9 rue des Orfèvres – 44840 Les Sorinières – France
 Phone : +33 (0)251 19 10 51 - Fax : +33 (0)240 05 73 81
 E-mail : contact@geneglace.com – www.geneglace.com