

2001 Evapco PMCB-Series Evaporative Condenser- 350 Tons

Mfg: Evapco

Model: PMCB 350

Stock No. CSRW005.

Serial No. W017199

2001 Evapco PMCB-Series Evaporative Condenser- 350 Tons. Model: PMCB 350. S/N: W017199. Last used with ammonia. Coil test pressure: 400 psig. Coil volume: 44 cu. ft. Air flow: 61,600 cfm. Evapco Pumps with US Motors, 5 hp, 1750 rpm, 208-230/460 V, 14.6-13.7/6.8 amps, 60 Hz, 3 phase. (2) 60 in. dia. fans with US Fan Motor, 10 hp, 1760 rpm, 230/460 V, 24.6/12.3 amps, 60 Hz, 3 phase. Evapco PMCB units are heavy-duty construction and designed for long trouble-free operation. Axial fan design. Inlets: (4) 6 in. dia. ports, (1) 4 in. dia. port, (1) 3 in. dia. port with 4-bolt flange. Outlets: (1) 6 in. dia. port, (1) 4 in. dia. port, (1) 5 in. dia. port with an 8-bolt flange, (1) 3 in. dia. port. Overall dimensions: 14 ft. 7 in. L x 9 ft. 10 in. W x 13 ft. 2 in. H.





