

## Frick Rotary Screw Compressor – 250 HP

**Mfg: Frick**

**Model: RWB II 100 H**

**Stock No.: DPFI427.3**

**Serial No.: S0029CFMPLHAA3**

Frick Rotary Screw Compressor. Model: RWB II 100 H. S/N: S0029CFMPLHAA3. Sales order No: 206473-01. Refrigerant: R717. Max speed: 3,600 rpm. MAWP: 300 psig. Teco Westinghouse motor, 250 hp, 3,550 rpm, 460 V, 279 amps, 60 Hz, 3 phase. Frick Oil Separator, Nat'l Bd: 54851, S/N: 226334, shell thickness: .375 in., head thickness: .375 in. MAWP 300 psig @ -20 to 200 °F. Frick oil cooler, S/N: MC-83070, shell thickness: .277 in., head thickness: .75 in. MAWP: 300 psig @ -20 to 200 °F. (2) Henry Technologies pressure relief valves, Cat No: 5601, set psi: 250, capacity 57.6 lbs air/min. Compressor Inlet: (1) 5 in. dia. suction pipe. Outlets: (1) 4 in. dia. discharge pipe. Overall dimensions: 11 ft. L x 4 ft. 3 in. W x 8 ft. 11 in. H. (ACN699a).



