

Kramer Air Cooled Condensing Unit

Mfg: Kramer

Model: C3F22KSH

Stock No. EEGC245.1

Serial No. E07860

Kramer Air Cooled Condensing Unit. Model: C3F22KSH, S/N: E07860. Refrigerant: R-22. Chiller barrel diameter: 6 in. Factory test pressure: high side 400 psi; low side 250 psi. Emerson Fan Motor: 1,075 rpm, 208-230 V, 1.3 amps, 60 Hz, 1 phase. Coplematic compressor: Model: ERF1-0311-TAD-800, S/N: 95C72883, 380-400/460 V, 50/60 Hz, 3 phase. Inlets/outlets: (1) 1/2 in. dia. copper tubing, (1) 3/4 in. dia. copper tubing. Overall dimensions: 43 in. L x 34 in. W x 40 in. H.

