



XLC Model ¹	NH ₃ Tons ²	CFM	Fan Mtr HP	Spray Water GPM	Pump Mtr HP	REMOTE SUMP			DIMENSIONS				Refrig Charge NH ₃ lb ⁵	WEIGHTS			Pan Heater kW
						Water In ³	Sump Drain ³	Gal. Req'd ⁴	Height H	Ctrs B	Width W	Base C		Unit Shipping ⁶	Unit Operating ⁷	Heaviest Section	
155	109.9	23,700	7.5	180	1	3*	5**	95	113.625	44.25	102.5	60	196	7,740	9,040	6,460	4.5
160	113.5	26,400	10	180	1	3*	5**	95	106.875	37.50	102.5	60	170	7,210	8,630	5,930	4.5
165	117.0	26,000	10	180	1	3*	5**	95	113.625	44.25	102.5	60	205	7,770	9,060	6,490	4.5
170	120.6	29,400	15	180	1	3*	5**	95	106.875	37.50	102.5	60	178	7,260	8,670	5,980	4.5
185	131.2	29,400	15	180	1	3*	5**	95	113.625	44.25	102.5	60	224	7,810	9,090	6,530	4.5
195	138.3	36,800	15	240	1.5	3*	6**	130	99.625	30.25	125.5	83	190	7,700	9,480	6,420	6
205	145.5	40,500	20	240	1.5	3*	6**	130	99.625	30.25	125.5	83	197	7,740	9,520	6,460	6
220	156.0	36,600	15	240	1.5	3*	6**	130	106.875	37.50	125.5	83	238	8,910	10,860	7,630	6
230	163.1	40,200	20	240	1.5	3*	6**	130	106.875	37.50	125.5	83	246	8,950	10,900	7,670	6
235	166.7	36,400	15	240	1.5	3*	6**	130	113.625	44.25	125.5	83	285	9,960	12,090	8,680	6
250	177.3	40,050	20	240	1.5	3*	6**	130	113.625	44.25	125.5	83	299	10,000	12,130	8,720	6
285	202.1	53,400	20	370	3	3*	6**	205	99.625	30.25	125.5	83	280	11,340	14,110	9,165	9
300	212.8	57,500	25	370	3	3*	6**	205	99.625	30.25	125.5	83	291	11,390	14,160	9,215	9
310	219.8	61,100	30	370	3	3*	6**	205	99.625	30.25	125.5	83	298	11,430	14,200	9,255	9
340	241.1	57,300	25	370	3	3*	6**	205	100.750	37.50	125.5	83	364	13,130	16,170	10,955	9
350	248.2	60,900	30	370	3	3*	6**	205	100.750	37.50	125.5	83	372	13,170	16,210	10,995	9
365	258.9	57,000	25	370	3	3*	6**	205	113.625	44.25	125.5	83	437	14,690	18,000	12,515	9
385	273.0	60,500	30	370	3	3*	6**	205	113.625	44.25	125.5	83	454	14,740	18,050	12,565	9
410-2	290.8	81,000	(2)20	480	(2)1.5	(2)3*	(2)6**	260	99.625	30.25	125.5	83	394	15,480	19,050	(2)6,465	(2)6
440-2	312.0	73,200	(2)15	480	(2)1.5	(2)3*	(2)6**	260	106.875	37.50	125.5	83	476	17,830	21,750	(2)7,640	(2)6
460-2	326.2	80,000	(2)20	480	(2)1.5	(2)3*	(2)6**	260	106.875	37.50	125.5	83	492	17,910	21,830	(2)7,680	(2)6
470-2	333.3	72,800	(2)15	480	(2)1.5	(2)3*	(2)6**	260	113.625	44.25	125.5	83	570	19,910	24,170	(2)8,675	(2)6
500-2	354.6	80,100	(2)20	480	(2)1.5	(2)3*	(2)6**	260	113.625	44.25	125.5	83	598	19,980	24,250	(2)8,715	(2)6
570-2	404.2	106,800	(2)20	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83	560	22,670	28,210	(2)9,160	(2)9
600-2	425.5	115,000	(2)25	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83	582	22,770	28,320	(2)9,210	(2)9
620-2	439.7	122,200	(2)30	740	(2)3	(2)3*	(2)6**	410	99.625	30.25	125.5	83	596	22,860	28,410	(2)9,250	(2)9
680-2	482.3	114,600	(2)25	740	(2)3	(2)3*	(2)6**	410	106.875	37.50	125.5	83	728	26,260	32,340	(2)10,955	(2)9
700-2	496.4	121,800	(2)30	740	(2)3	(2)3*	(2)6**	410	106.875	37.50	125.5	83	744	26,340	32,430	(2)10,995	(2)9
730-2	517.7	114,000	(2)25	740	(2)3	(2)3*	(2)6**	410	113.625	44.25	125.5	83	874	29,380	36,010	(2)12,520	(2)9
770-2	546.1	121,000	(2)30	740	(2)3	(2)3*	(2)6**	410	113.625	44.25	125.5	83	908	29,470	36,100	(2)12,570	(2)9

*Male Pipe Thread **Female Pipe Thread