

## I.J. White Spiral Freezer

Mfg: I.J. White

Model:

Stock No: MDFP122A


Serial No:

I.J. White Spiro-Freeze Spiral Freezer. Bottom Load "Up Go" Design. I.J. White control panel. Cramer hour meter: 52,163 hrs. Belt dimensions: 850 ft. L x 26 in. W x 3-1/4 in. H. (\*NOTE: Spiral with Uninstalled Belt). Belt material: stainless steel. Drum frame model: 26-AL-579-F-B. Drum size: Est. 14 ft. Dia. Number of tier: 18. Drum frame material: Aluminum. Belt speed: 90 FPM. Dwell time: 17 Min. Controls including Reliance and Allen Bradley VFD's. Main drum drive motor – 7.5 hp, 300-1800 rpm, 230/460 V, 18.8/9.4 amps, 60 Hz, 3 phase. Sew euro drive. Ratio: 115.63, Out: 2.6 – 16 rpm, In: 300-1800 rpm, Torque: 31,777.

### Installed:









**Dismantled:**























Chap 17-26 W

IN FEED  
Down Low  
coil

UP HIGH  
CHANGE OVER  
TO SECOND SPIRAL  
coil

OUT FEED  
AT Bottom



16 FT

7 FT

16 FT

16 FT