



**NOTES:**

1. (M) - FAN MOTOR LOCATION
2. MAKE-UP WATER PRESSURE 20psi MIN. 50psi MAX.
3. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DWG.
4. ALL NIPPLE LOCATIONS ARE APPROXIMATE DIMENSIONS. DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING.
5. HEAVIEST SECTION IS UPPER SECTION
6. SERIES FLOW CONN. AND AUXILIARY CROSSOVER DRAIN BY OTHERS.

MODEL	WEIGHTS			DIMENSIONS			NO. SHIPPING SECTIONS
	SHIPPING	OPER.	HEAVIEST SECTION	H	C	R (4)	
ATW 33A2	3720	6060	3110	8'-5-1/4"	5'-9-3/4"	19-1/2	2
ATW 33B2	4330	6900	3730	9'-3/4"	6'-5-1/4"	27	2
ATW 33C2	4990	7780	4380	9'-8-1/4"	7'-3/4"	34-1/2	2

CERTIFIED FOR Arctic Air Inc. PROJECT: Mariano Bros. TAG \_\_\_\_\_  
 CUSTOMER ORDER NO. 6631 EVAPCO NO. 941728  
 CAPACITY 98 GPM of water 95 'IN 85 'OUT 78 'W.B.  
 FAN MOTOR (2) 3 H.P. ELEC. SPEC. 208/60/3  
 PUMP MOTOR (1) 1 H.P. ELEC. SPEC. 208/60/3  
 REMARKS Split Circuit Coil for series flow. Unit furnished with (1) 4kW pan heater,  
 208/60/3, with thermostat and low water cutoff. Coil pressure drop 3 psi.  
 Drives sized for 0" ESP.



CLOSED CIRCUIT  
COOLER

REV DMP DATE 10/26/94

WA0409AD-006