

Frick LDB 26 Booster Rotary Screw Compressor Package – 50 HP

Mfg: Frick

Model: LDB 26

Stock No: HDPW733.5

Serial No: MC-80164

Frick LDB 26 Booster Rotary Screw Compressor Package. Model LDB 26, S/N MC-80164. Nominal capacity: Westinghouse electric motor, 50 hp, 3523 rpm, 230/460V, 117/58.5 amps, 60 Hz, 3 phase. Frick oil separator, Nat'l Bd: 44451, MAWP: 150 psig at -20°F to 200°F. Shell and head thickness: .375 in. Radius: 2/1. Frick oil filter housing, S/N: MC-80164, MAWP: 300 psig at -20°F to 200°F. Shell thickness: .277 in. Head thickness: .75 in. Radius: flat. Liquid injection cooling. Unit has a simple, on/off Frick control panel. Inlet: 4 in. suction. Outlet: 2 in. discharge. Overall dimensions: 9 ft. 4 in. L x 3 ft. 3 in. W x 7 ft. H.





