

Stainless Steel Single Shell Mixing Tank- 280 Gallon

Mfg:

Model:

Stock No. RFPM191.1

Serial No. _____

Stainless Steel Single Shell Mixing Tank- 280 Gallon. Tank sits vertically and is equipped with a 30 in. W x 62 in. H agitator that produces even mixing. Cone bottom. Motor, 1780 rpm, 208-230/460 V, 6.4-6.4/3.2 amps, 60 Hz, 3 phase. Boston Gear Reducer, 60 ratio, 29.6 rpm (final). Inlets: open top. Outlets: (1) 4 in. dia. S-line fitting. Overall dimensions: 46 in. L x 35 in. W x 10 ft. 2 in. H.



