



NOTES:

1. MAKE-UP LOCATED 4-3/4" FROM CONNECTION END
2. MAKE-UP WATER PRESSURE 20 PSI MIN. 50 PSI MAX.
3. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DRAWING
4. ALL NIPPLE LOCATIONS ARE APPROXIMATE DIMENSIONS. DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING
5. SERIES FLOW CONN. AND AUXILIARY CROSSOVER DRAIN BY OTHERS

MODEL	WEIGHTS			DIMENSIONS			NO. SHIPPING SECTIONS
	SHIPPING	OPER.	HEAVIEST SECTION	H	C	R (4)	
ATM 91A2	9670	15130	7720	11'-1-3/4"	6'-10"	19-1/2	2
ATM 91B2	11330	17390	9370	11'-9-1/4"	7'-5-1/2"	27	2
ATM 91C2	13000	19560	11040	12'-4-3/4"	8'-1"	34-1/2	2

CERTIFIED FOR State Refrigeration PROJECT: Pet Incorporated TAG _____
 CUSTOMER ORDER NO. 111578 EVAPCO NO. 906677
 CAPACITY 217 GPM of 35% Ethylene Glycol 99.2° IN 82° OUT 77° W.B.
 FAN MOTOR (1) 20 speed/1 wind. H.P. ELEC. SPEC. 460/60/3
 PUMP MOTOR (1) 3 H.P. ELEC. SPEC. 460/60/3
 REMARKS Unit arranged for series flow, furnished with (2) 6kW pan heaters, 480/60/3,
with thermostat and low water cutoff. Coil pressure drop 6.4 psi. Drives sized for 0" ESP.



CLOSED CIRCUIT COOLER

REV ms DATE 12/4/90

WA0812AB-006