

Reco Evaporative Condensing Tower – 625 Tons

Mfg: Reco

Model: RA-919E

Stock No: KWBF213



Serial No: 879999

Reco Evaporative Condensing Tower. Model: RA-919E. S/N: 879999. Nominal rated capacity: 625 tons using R-22 at 105°F condensing, 40°F suction and 78°F wet bulb temperatures. 450 tons using R-717 at 96.3°F condensing, 20°F suction and 78°F wet bulb temperatures. Coil test pressure: 350. Belt No: 2B-133. Number of axial fans: 3. Fan diameter: 5 ft. (2) Fan motors: Magnetek electric motor: 10 HP, 1745 rpm, 230/460 V, 24/12 amps, 60 Hz, 3 phase. Centrifugal pump. Model: 5G. S/N: 74126-1. Baldor Electric pump motor: 7.5 HP, 1,760 rpm, 208-230/460 V, 21.6/10.8 amps, 60 Hz, 3 phase. Inlets: (2) 1 ft. 8 in. manway ports, (1) 6 in. dia. port, (2) 4 in. dia. ports, (1) 2 in. dia. ports. Outlets: (1) 6 in. dia. port, (2) 4 in. dia. ports, (2) 3 in. dia. ports. Overall dimensions: 21 ft. 2 in. L x 10 ft. W x 17 ft. 2 in. H.









The Following are Pictures of the Previous Installation.

