

## Kramer CTT Thermobank Condensing System- 40 Ton

Mfg: Kramer



Model: CTT24200M34X

Stock No. RPAG1402A.11a

Serial No. A0026019.011

Kramer CTT Thermobank Condensing System- 40 Ton. Model: CTT24200M34X. SN: A0026019.011. (20 tons at 30F) Outdoor use. Refrigerant: R-134. Design pressure lo/hi: 180/450 psig. Mid-temperature. Minimum supply: 118 amps, Maximum supply: 150 amps. (4) 30 in. dia. Condenser Fans, 1.5 hp (each), 460 V, 3.2 amps, 60 Hz, single phase. (2) Copeland Discus Compressors, Models: 4DJ3-200E-TSK-200 and 4DJ3-200E-TSK-800, S/N's: 99104175 and 00174678, 460 V, 33 RLA, 173 LRA, 60 Hz, 3 phase. The Thermobank delivers more refrigeration with less energy consumption, less equipment, less installation and lower operating cost. Thermobank is available for all commercial and industrial applications. Less equipment is needed with Thermobank because it does more refrigeration in 24 hours than any other package system and also has the fastest defrost period (typically 5 to 10 minutes). Inlets: (1) 2-1/2 in. dia. copper port, (1) 1 in. dia. copper port. Outlets: (1) 2-1/2 in. dia. copper port, (1) 1 in. dia. copper port. Overall dimensions: 12 ft. 7 in. L x 93 in. W x 50-1/2 in. H.





Includes these options:  
Includes (2) 20 Hp Compressors  
134a Refrigerant  
Tonnage - 20 Tons With +20 Suction

Options Below:

1.00	1	1 Rcu	Condensing 1
Options Begin.....			
1.02	1	1 99999	Discontinu
1.		P/N Ctt2-4200m34x	
2.		Thermobank Condensing Unit	
3.		460/3/60	

With (2) 4dj3-200e Compressors  
Piped & Wired Independently  
On A V Series Chassis  
With A Vac 68 Condenser  
With 115v Control Circuit Power  
With Thru-The-Door Disconnect  
With Oversized Receiver With Inlet & Outlet  
Service Valves  
With Pressure Relief Valve  
With Replaceable Core Liquid Line Filter Drie  
With Replaceable Core Suction Line Filter  
With 100 Pound Flood Valves  
With Individual Condenser Fan Motor Contactors  
With (1) Step Temperature Fan Cycling Per Circuit  
(Pilot Duty)  
With Individual Sub-Circuit Fusing  
(Per Kramer Standard Practice)  
With Anti-Short Cycle Timer  
With Phase Loss Monitor  
With Single Point Alarm  
With Hi/Low Oil Pressure Gauges  
With Pumpdown & Compressor Start Switches  
With Sentronic Oil Safety Controls  
With Flexible Control Lines  
With Discharge Line Mufflers  
With Photo Etched Plate Wiring Diagrams  
With Liquid Line Service Valve