

## Un-Used Baltimore Aircoil Company CXV Evaporative Condenser – 320 Tons

**Mfg: Baltimore Aircoil Company**

**Model: CXV-253**

**Stock No.: NBAC01.255**

**Serial No.:**

Un-Used Baltimore Aircoil Company CXV Evaporative Condenser. Model CXV-253. Approximate capacities: 320 tons using R-22 at 105°F condensing temperature, 40°F suction temperature and 78°F wet bulb temperature, and 253 tons using R-717 at 96.3°F condensing temperature, 20°F suction temperature and a 78°F wet bulb temperature. Airflow rate: 76,800 cfm. Design features of the CXV series satisfy today's environmental concerns, minimize installation costs, maximize year-round operating reliability, and simplify maintenance requirements. (1) 15 hp fan motor. (1) 5 hp pump motor. Approximate shipping weight: 11,830 lbs. Condenser dimensions: 12 ft. 1-1/4 in. L x 11 ft. 10 in. W x 15 ft. 10-3/4 in. H.(ACN366a)

### CXV Evaporative Condensers

- Reduced Refrigerant Charge
- Low Energy Consumption
- Low Installed Cost
- Easy Maintenance
- Reliable Year-Round Operation
- Long Service Life
- ASME B31.5 Compliant Coils
- Five-Year Warranty on Mechanical Equipment

Model	Tons @ 70°F WB	MBH @ 70°F WB	Tons @ 75°F WB	MBH @ 75°F WB	Tons @ 78°F WB	MBH @ 78°F WB	Tons @ 80°F WB	MBH @ 80°F WB
CXV-253	337.3	5,141.1	284.3	4,351.8	253.0	3,855.8	227.9	3,472.8

