

Evapco Evaporative Condenser – 35 Tons

Mfg: Evapco

Model: LSC-35

Stock No: RPCN441B

Serial No: 813499 LH

Evapco Evaporative Condenser. Model: LSC-35. S/N: 813499. Nominal capacity: 35 tons using R-22 at 40°F suction, 105°F condensing and 78°F wet bulb. Rated at 25 tons using R-717 at 20°F suction, 96.3°F condensing and 78°F wet bulb. Coil maximum working pressure rated at 350 PSIG. Number of fans: (2). Belt #: B-90. (1) Baldor fan motor, 2 hp, 1725 rpm, 208-230-460 V, 6.8-6.4/3.2 amps, 60 Hz, 3 phase. Unit was used in a remote sump application and does not include a pump. The LSC model is a centrifugal fan, forced draft condenser that is quiet and ideal for applications where noise is a concern. Centrifugal fans assist in counteracting static pressure loss related to ductwork and these units are suitable for indoor installations where it is desirable to hide the unit, or when this is the only space available. Left hand unit. Copper sweat fittings have been removed. (1) 1 ft. 8 in. manway. Inlets: (2) 2 in. port. (1) 2 in. port. Listed shipping weight: 2410 lbs. Overall dimensions: 6 ft. 7 in. L x 4 ft. 11 in. W x 7 ft. 6 in. H.







