

Crepaco Scrape-Surface Jacketed Processing Tank- 700 Gallon

Mfg: Crepaco

Model:

Stock No. pRCPK386.22a

Serial No. D-4074

Crepaco Scrape-Surface Jacketed Processing Tank- 700 Gallon. S/N: D-4074. National Board: 5893. Inside dimensions (straight wall): 66 in. dia. x 36 in. H. Jacket MAWP: 109 psi @ 400 °F. Inner lining pressure unloading: 15 psi. Heat exchanger jacket: 75 psi. (2) Rigid-rigid baffles, each with (4) blades. Bottom-scrape surface agitator also equipped with revolving blades. (2) Manways: 17-3/4 in. dia. Reliance Electric Motor (mixer), 10 hp, 1755 rpm, 230/460 V, 27/13.5 amps, 60 Hz, 3 phase. Reliance Electric Master XL Motor Drive, 70 ratio, 25 rpm (final). Inlets: (1) 6-1/2 in. dia. pipe, (1) 3 in. dia. 'S' line fitting, (1) 3 in. dia. NPT (male), (1) 2-1/2 in. NPT (male), (2) 1-1/2 in. dia. 'S' line fitting, (1) 2 in. dia. NPT (male, jacket). Outlets: (1) 4 in. dia. 'S' line pneumatic-valve (tank discharge), (1) 1-3/4 in. dia. NPT (male, jacket). Overall dimensions: 78 in. diameter x 11 ft. H.



