

York Water Cooled Chiller- 50 Tons

Mfg: York

Model: YCW-E05-17PD

Stock No. DBHK201.0

Serial No. YCW179639

York Water Cooled Chiller- 50 Ton. Model YCW-E05-17PD. S/N YCW179639, ID York-1, 151.805 kcal/hr, with wall-mounted breaker switch box. Indoor use voltage limits 180-220. 200 volt, 3 ph, 60 Hz. 3 in. power supply inlet to box. Refrigerant: R-22. Test pressure: 300 psi high side; 150 psi low side. Minimum circuit capacity: 298 amps. York compressor, Model JS63F-NFA, S/N SMRP1065502. Date code 9020703, 200 V, 3 phase, 60 Hz. Refrigerant: R-22. Unit control panel power supply: 115 V, 2 phase, 60 Hz. Oil heater: 115 V, 1 phase, 60 Hz, 350 watts. Compressor: 200 V, 3 phase, 60 Hz. National Board No. 61966. Shell: 300 psi at 20 to 250 °F. Tube chamber: 150 psig at 20 to 120 °F. Overall dimensions: 101 in. L x 36 in. W x 54 in. H.

