

Waukesha Model 60 Positive Displacement Pump

Mfg: Waukesha

Model: 60

Stock No: DWKN217.10

Serial No: 2027-SS

Waukesha Positive Displacement Pump. Model: 60. S/N: 2027-SS. Flow rate for new pump is 90 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Maximum pressure: 200 psi. Maximum speed: 600 rpm. Temperature range: -40°F to 300°F. U.S. Syncrogear motor: 2 hp, 1725 rpm, 230/460 V, 6.4/3.2 amps, 60 Hz, 3 phase. Drive ratio: 5.07, rpm out: 340 (final). Features include: easy cleaning and disassembly, three-way mounting options, non-galling Waukesha "88" alloy rotors, 316 stainless steel pump body, cover and shaft, and O-ring seal option. Inlets/outlets: (2) 2-1/2 in. dia. ACME fittings. Overall dimensions: 3 ft. 4 in. L x 1 ft. W x 1 ft. 9 in. H.(ACN109a).





