

2001 Waukesha Model 5040 Positive Displacement Pump

Mfg: Waukesha

Model: 5040

Stock No: MPEC03.1

Serial No: 283643 01

2001 Waukesha Positive Displacement Pump. Model: 5040, S/N: 283643 01. Flow rate for new pump is 36 gpm with required horsepower and pressure. Discuss with salesperson your process and product to determine if this refurbished pump should handle your specific duty. Max rpm: 600. Max. pressure: 200 psi. Temperature range: -40 °F to 300 °F. The model 5040 is a self-priming, reversible, high-efficiency rotary pump configured for a wide variety of industrial applications including pumping low viscosity and non-lubricating fluids, metering fluids, shear-sensitive fluids, or for pumping high-viscosity fluids at low rates of flow. Typical product applications include solvents, oils, lubricants and other products such as acids, animal fats, soaps, and sludge. Inlets / outlets: (2) 1-3/4 in. dia. FPT fitting. Overall dimensions: 1 ft. 6 in. L x 8 in. W x 11 in. H.(ACN 51).

