

Waukesha Model 060 Positive Displacement Pump

Mfg: Waukesha

Model: 060

Stock No: AAC4356.17

Serial No: 197741 97

Waukesha Model 060 Positive Displacement Pump. S/N: 197741 97. Flow rate for a new pump is 90 gpm at max rpm of 600. Discuss with salesperson your process and product to determine if this pump should handle your specific duty. Pump currently has O-ring seals. Drive and pump seals can be changed to suit your application. Baldor motor: 5 hp, 208-230/460 V, 15-13.2/6.6 amps, 1725 rpm, 184TC frame, 60 Hz, 3 phase. Inlet/outlet: 2.5 in. S-line fittings. Overall dimensions: 4 ft. 1 in. L x 1 ft. 2 in. W x 1 ft. 6 in. H.



