

Manton Gaulin Homogenizer Size 3. Model: 88 M3-8TBS

Mfg: Gaulin

Model: 88 M3-8TBS

Stock No. 195.GR940.

Serial No. 3673514

Manton Gaulin Homogenizer. Model: 88 M3-8TBS. Size: 3. 2-stage manual valve assembly. 3/4 in. dia. plungers. 8,000 psi. Tapered seat ball valve cylinders. Minimum capacity: 50. Maximum capacity: 120 gph. S/N 3673514.

Painted frame. Ball valve diameter: 7/8 in. Casters provide easy positioning. U.S. Motor, 10 hp, 1740 rpm, 670 rpm (final), 208-230/460 V, 29.2-27.5/13.75 amps, 60 cycles, 3 phase. Motor pulley diameter: 4-3/8 in. Gear pulley diameter: 11-3/8 in. Approximate weight: 1500 lbs. Inlets/outlets: (2) 1-1/2 in suction/discharge. Inlets: (1) 1 in. dia. threaded fitting. Outlets: (1) 3/8 in. dia. threaded fitting. Overall dimensions: 39 in. L x 35 in. W x 51-1/2 in. H.

