

Sandpiper Dual Diaphragm Stainless Steel Pump

Mfg: Sandpiper

Model:

Stock No: AANF119.5

Serial No:

Sandpiper Double Diaphragm Stainless Steel Pump, 2 in., Pneumatic Powered. This appears to be a G20 Metallic design level 1 ball valve unit. Nameplate missing. The G20 has these specs: .42 gallon displacement, 150 GPM max flow, 0.25 inch solids handling, and max discharge of 100 PSI.





