

RECO Cascade IQF Freezer

Mfg: RECO

Model: 100

Stock No: AANF046.90

Serial No: M18027-230

RECO Cascade IQF Freezer with enclosed box (approx. 11 ft. x 34 ft.), hydraulic drives and components, and circulation tank. Model: 100. S/N: M18027-230, Rated capacity(peas): 10,000 lbs. per hour from respective inlet and outlet temperatures of 70°F to 0°F with required tonnage rating and sustained recirculated evaporation temperature. Other vegetables will vary. Belt width: 59 in., loading belt height: 8 ft. 3 in., discharge belt height: 7 ft. RECO's unique design provides a sequence of fluidization stages that utilize varied properties of incoming products by uniformly glazing (1/2 in. to 2 in.) in the first stage, and then moving to a second stage ranging from 4 in. to 8 in. for dense fluidization, all from low temperature air directed from beneath the belt. Listed shipping weight: 35000 lbs. Overall dimensions: 41 ft. L x 11 ft. 6 in. W x 12 ft. H.







RICO SPEED

		INFEED	DISCHARGE
DICED	IQF DEHYDRO	8 SEC	11 SEC
SLICED	IQF DEHYDRO	12 SEC	22 SEC
SLICED	IQF	16 SEC	26 SEC
DICED	IQF 545	8 SEC	24 SEC
DICED	IQF 533	6 SEC	18 SEC
DRYUSED	BLUEBERRIES	8 SEC	18 SEC
FRESH	BLUEBERRIES	12 SEC	24 SEC