

Stainless Steel Pass Through Tote Washer – 24 in. W

Mfg:

Model:

Stock No: AANF449.16

Serial No:

Stainless Steel Pass Through Tote Washer with 24 inch wide plastic conveyor belt. Conveyor frame, sump, cover, and filtration components are made of stainless steel. The unit does not have self-heating capability. Circulation and spray piping is PVC. Conveyor belt is modified for a previous application with 16 in. wide cutouts (24 in., 26in., and 32.25 in. long). Top spray piping is approximately 9.5 inches above belt. Conveyor drive: 1 HP, 208-230/460V, 3.6-3.4/1.7 Amps, 60 Hz, 3-phase. Ampco centrifugal pump, model: 2.5 x 2 DC2, S/N: CC-10987-1-1, 3500 RPM, 4.875 in. impeller dia. Motor: 5 HP, 208-230/460V, 13.2-12/6 Amps, 3450 RPM, 60 Hz, 3-phase. Ampco centrifugal pump, 2.5 x 2 ZC2, 4.875 in. impeller dia, 3500 RPM, s/n: V-56928-1-2. 5 HP, 208-230/460V, 13.2-12/6 Amps, 3450 RPM, 60Hz, 3-phase. Cleaning real motor: 1/3 HP, 230/460V, 1.7/1.85 Amps, 1725 RPM, 3-phase, 60 Hz. Dual Rosedale filters: model 8-30-2SN-1-150-SVSB, max 150 PSI. Interior spray piping material: PVC plastic. Waste flume (drain channel included). Wash tank dimensions (approx.): 3 ft. W x 14 ft. L x 3 ft. H. Overall length: 16 ft.



