

## Stainless Steel Screw Auger Conveyor- 14 Ft

Mfg:

Model:

Stock No. AARF100.

Serial No.:

Stainless Steel Screw Auger Conveyor- 14 Ft. Screw auger dimensions: 12 in x 12 ft. 6 in. L. Pitch: 7-3/4 in. Infeed hopper dimensions: 35 in. L x 15 in. W. Guard screen has openings that are 3-1/4 in. L x 3-1/4 in. W. Leeson Washguard Motor, 3 hp, 1770 rpm, 208-230/460 V, 60 Hz, 8.2 FLA, 3 phase. LinkBelt/PrimeGear Speed Reducer, 15.09 ratio, 1750 input rpm, 117.29 final rpm, 109 in. torque. Inlets: (1) 24 in. L x 12 in. W infeed. Outlets: (1) 13 in. L x 13 in. W discharge. Overall dimensions: 15 ft. 4 in. L x 45 in. W x 42 in. H.

