



NOTES:

- (1) ALL HANGER HOLES ARE 13/16Ø, ALL LEGS ARE REMOVABLE.
- (2) THE EVAPORATOR CONNECTION SIZES (SHOWN) DO NOT NECESSARILY COORESPOND TO THE APPROPRIATE SYSTEM PIPE SIZES.
- (3) DO NOT SCALE DRAWING. CONNECTION LOCATIONS ARE APPROXIMATE, DO NOT USE FOR FABRICATION OF PIPING.
- (4) 5.0 PSI LIQUID FEED PRESSURE REQUIRED ABOVE COIL SATURATED SUCTION PRESSURE.

***HANGER HOLE LOCATIONS**

QTY. 1	MODEL SSTM4-01988-4	SERIAL NUMBER 5-130447	CERTIFIED FOR	PROJECT	
PERFORMANCE DATA: <u>24.854</u> TONS (<u>298,245</u> BTUH) @ <u>15°F</u> TD <u>35°F</u> ROOM TEMP. <u>20°F</u> SST <u>R-717</u> REFRIGERANT <u>BOTTOM</u> FEED <u>20°F</u> LIQ. FEED TEMP. <u>3:1</u> RECIRC. RATE <u>85</u> dBA @ 6 FT PER UNIT, FREE FIELD		FAN/MOTOR DATA: <u>21,975</u> CFM @ <u>0"</u> ESP <u>589</u> FPM FACE VELOCITY <u>(4)</u> <u>0.5</u> HP TEAO FAN MOTOR(S) <u>1160</u> RPM <u>460/3/60</u> SERVICE <u>1.4</u> DESIGN MOTOR AMPS <u>30"</u> FAN DIAMETER		PHYSICAL DATA: <u>37.3</u> SQ. FT. FACE AREA <u>3.65</u> CU. FT. COIL VOLUME <u>8</u> ROWS DEEP <u>4</u> FPI <u>2,161</u> LBS. NORMAL OPERATING WEIGHT <u>1,860</u> LBS. SHIPPING WEIGHT	ROOM <u>35°F ROOM</u> REFERENCE APP. VERSION 1.9.16
REMARKS: STAINLESS STEEL TUBE, ALUMINUM FIN COIL, STAINLESS STEEL CASING, PAN AND PAN COVER, HOT GAS DEFOST, COIL ONLY.					
 P.O. Box 1300 Westminster, Maryland 21158 USA Phone (410)756-2600 Fax (410)756-6450 REV:1) 07/11/05 tm DATE: 07/11/05 TAW					



--- DASHED LINES REPRESENT
WIRING BY OTHERS

— SOLID LINES REPRESENT
WIRING BY EVAPCO

REV:1) 07/11/05 tm

QTY. 1	MODEL SSTM4-01988-4	SERIAL NUMBER 5-130447	CERTIFIED FOR	PROJECT
CONFIDENTIAL This document is the property of Evapco, Inc. It should not be copied or disclosed without prior written authorization.			TITLE ELECTRICAL SCHEMATIC	DRAWN BY TAW CHECKED BY
				EVAPCO, INC.