

1999 Pavan Toresani / Foodmac Cascading Belt Pre-Dryer

Mfg: Pavan

Model: E4X5R15

Stock No.: ATGP204

Serial No.:

1999 Pavan Toresani / Foodmac Cascading Belt Pre-Dryer. Type: E4X5R15. Stainless steel chain belt width: 4 ft. 10 in. Number of belt sections: 5. Belt specifications - rod diameter: 0.190 in., pitch: 4 in., base gap: 0.130 in. Power supply: 6.7 hp (5 kW), 480V, 60 Hz. Evaporator, number of tubes: 36, tube dimensions: 1-1/2 in. dia. x 9 ft. 4 in. L. ABB Electric Belt Motor with Speed Reducer, 2 hp, 1410/1720 rpm, 380/420-220/240-440/480-255/275 V, 3.3/5.7-2.9/5.0 amps, 50/60 Hz, 3 phase. (4) Bonfiglioli Worm Gear Drives, Model: VF49. ABB Electric Belt Motor, 2 hp (1.5/1.75 kW), 1420/1720 rpm, 380/420-220/240-440/480 V, 3.5/6.1/3.5 amps, 50/60 Hz, 3 phase. Bonfiglioli Worm Gear Drive. Number of fans: 4. Fan diameter: 1 ft. 7 in. ABB Electric Fan Motor, 0.49/0.60 hp, 1420/1700 rpm, 380/420;220/240-440/480;250/280 V, 1.1/1.9 amps, 50/60 Hz, 3 phase. (3) ABB Electric Fan Motors, 1/1.2 hp, 1420/1700 rpm, 380/420;220/240-440/480 V, 2-3.5/2 amps, 50/60 Hz, 3 phase. MZ Aspiratori Electroaspiratore Centrifugal Blower, Model: CA200, S/N: 19709566, fan diameter: 7 in. Leeson Electric Blower Motor, 1.5 hp, 2850/3400 rpm, 230/460 V, 4.0/2.0-4.4/2.2 amps, 50/60 Hz, 3 phase. Conveyor infeed height: 5 ft. 6 in. Conveyor exit height: 2 ft. 6 in. Inlets: (1) 1/2 in. dia. liquid port, (1) 1 in. dia. refrigerant feed port. Outlets: (1) 1-1/2 in. dia. refrigerant suction port. Overall dimensions: 16 ft. 1 in. L x 8 ft. 4 in. W x 9 ft. 8 in. H.





























