



VIEW A-A

NOTES:

1. (M) - FAN MOTOR LOCATION
2. MAKE-UP WATER PRESSURE 20 psi MIN. 50 psi MAX.
3. 3/4" DIA. MOUNTING HOLES. REFER TO RECOMMENDED STEEL SUPPORT DWG. No SP1859
4. X - APPROXIMATE DIMENSION. DO NOT USE FOR PREFABRICATION OF CONNECTING PIPING
5. VIEW B-B SAME AS VIEW A-A LESS MAKE-UP AND DRAIN CONNECTIONS, AND OPPOSITE HAND

REVISION No.2

MODEL	WEIGHTS			DIMENSIONS		
	SHIPPING	OPER.	HEAVIEST SECTION	H	C	R
PMCA 990	37800	54220	12380	12'-6-1/4"	3'-11-3/4"	22-1/4"
PMCA 1060	44070	61190	15500	13'-2-3/4"	4'-8-1/4"	30-3/4"
PMCA 1170	44470	61590	15500	13'-2-3/4"	4'-8-1/4"	30-3/4"
PMCA 1250	44780	61900	15500	13'-2-3/4"	4'-8-1/4"	30-3/4"
PMCA 1290	50880	68700	18860	13'-11-1/4"	5'-4-3/4"	39-1/4"
PMCA 1370	50990	68810	18860	13'-11-1/4"	5'-4-3/4"	39-1/4"
PMCA 1430	57600	76130	21870	14'-7-3/4"	6'-1-1/4"	47-3/4"
PMCA 1510	58140	76640	21870	14'-7-3/4"	6'-1-1/4"	47-3/4"



evaporative condenser

CERTIFIED FOR: \_\_\_\_\_

CUSTOMERS ORDER NO. \_\_\_\_\_ EVAPCO NO: 940983  
 CAPACITY 887 TR R-717 REFRIG 96.3°F COND +20°F SUCT 78°F W.B.  
 FAN MOTOR (2) 20 & (2) 10 H.P. ELEC. SPEC. 230,460/60/3  
 PUMP MOTOR (2) 7-1/2 H.P. ELEC SPEC. 230,460/60/3  
 REMARKS Drives sized for 0" ESP.

REV: