

Thermo King Corporation Electric/Diesel Refrigerated Box

Mfg: Thermo King

Model: KD II-50

Stock No.: ATGP009.50

Serial No.: 0813124585

Thermo King Corporation Electric/Diesel Refrigerated Box. Inside dimensions: 20 ft. L x 7 ft. 4 in. W x 7 ft. 6 in. H. 1990 Thermo King Refrigeration Unit, Model: KD II-50, S/N: 0813124585, refrigerant: R-12, R-502, power supply: 230 V, 60 Hz, 3 phase. Thermo King Diesel Engine, Model: TK3.66, S/N: K23702, displacement: 40 cu. in. (0.658 L), compressor run time: 8,596 hrs. Thermo King Electric Motor, 5 and 4.2 hp, 1750/1450 rpm, 230/460-220/380 V, 14.4/7.2-12.7/7.3 amps, 60/50 Hz, 3 phase. Todco Overhead Truck Door. Inlets: (1) 7 ft. 6 in. L x 7 ft. 4 in. W (rear access door). Outlets: (1) 6 ft. 8 in. L x 3 ft. 4 in. W (passenger access door). Overall dimensions: 23 ft. 3 in. L x 8 ft. W x 9 ft. 3 in. H. (ACN507).







