

Shell and Tube Heat Exchanger

Mfg:

Model:

Stock No. 8.BR-398.2

Serial No.:

Shell and Tube Heat Exchanger. Stainless steel construction. 7-1/2 in. dia. flanged ends with (4) 3/4 in. dia. thru-holes at a center-to-center distance of 4-1/4 in. Inlets: (3) 3/4 in. dia. stainless steel tubes, (1) 3/4 in. dia. NPT (female, cover), (1) 3/4 in. dia. NPT (female, pressure relief), (1) 1 in. dia. NPT (female, shell). Outlets: (1) 3/4 in. dia. NPT (female, pressure relief), (1) 1 in. dia. NPT (female, shell). Overall dimensions: 7-1/2 in. dia. x 11 ft. L.



