

**Fristam FKL-150 Positive Displacement Pump - 15 HP**

**Mfg: Fristam**

**Model: FKL-150**

**Stock No.: CAGC1053**

**Serial No.: 007717**

Fristam rotary lobe positive displacement pump. Model FKL-150. Serial 007717. Max pressure: 300 PSI. Displacement per revolution: 0.259 gallons. Max flowrate: 155.4 gallons per minute at 600 RPM. GE motor: 15 HP, 208-230/460V, 38.5-34.8/17.4 amps, 1760 RPM, 254TCY frame, 60 Hz, 3-phase, TE. Nord gear reduction drive: 14.00 ratio (125 final RPM, 32.4 GPM). Stainless steel base. Ports: 3 in. clamp. (ACN115)



