

Durco Mark II Self Priming Centrifugal Pump

Mfg: Durco

Model:

Stock No. BR-56.4a

Serial No. 162686

Durco Mark II Self Priming Centrifugal Pump. Size: 3x2S-13/110. S/N: 162686. Capacity: 325 gpm @ 100 tdh and 8 ft. NPSH. Alloy: D20 (Durimet 20). Westinghouse Motor, 15 hp, 1765 rpm, 460 V, 19.5 amps, 60 Hz, 3 phase. The Durco Mark II pump is ideal for emptying sumps, unloading tank cars, or wherever the liquid level is below the pump. The pump primes quickly and recovers broken prime fast. This pump sits by the side of the sump, not in it. Inlet: (1) 3 in. dia. flanged suction port. Outlet: (1) 2 in. dia. flanged discharge port. Overall dimensions: 62 in. L x 23 in. W x 40 in. H.



