


Revised 9/20/94 CJP



\* 4.6 PSI LIQUID FEED PRESSURE  
REQUIRED ABOVE COIL SATURATED  
SUCTION PRESSURE.

QTY. **12** MODEL **NTL3-99103-750M** CERTIFIED FOR **SUPERIOR INDUSTRIES- 941290-301** PROJECT **W. POINT WAREHOUSE PROJECT**

PERFORMANCE DATA:  
608,910 BTUH AT 10° F TD  
-20° F ROOM TEMP. -30° F SST  
R-717 REFRIGERANT BOTTOM FEED  
-30° F LIQ. FEED TEMP. 3:1 RECIRC. RATE  
5 PSIG LIQ. FEED PRESS.

FAN DATA:  
88,014 CFM @ 0° ESP  
885 FPM FACE VELOCITY  
(3) 7.5 HP FAN MOTORS  
1,750 RPM TEAO TYPE  
460 / 3 / 60 SERVICE  
96 dBA @ 6 FT.

PHYSICAL DATA:  
 EXCLUSIVE THERMAL-PAK FINNED COIL  
 (PATENT PENDING)  
99.5 SQ. FT. FACE AREA  
10 ROWS DEEP 3 FPI  
26.04 CU. FT. COIL VOLUME  
9,663 LBS. SHIPPING WEIGHT

ROOM **BLAST FREEZER (CS)**  
 REFERENCE PAGE



P.O. Box 1300  
 Westminster, Maryland 21158 USA  
 Phone (410)756-2600  
 Fax (410)756-8450

REMARKS: Motors Pre-Wired to Individual Junction Boxes. Hot Gas Defrost Coil and Pan.

REV 1 DATE 8/11/94